



# Mask II Plus



## Respiratory protection: half masks

### Description and composition:

#### Manufactured in natural, odourless rubber.

The half mask's matte finish does away with bothersome reflections and reduces dirt adherence. Improved contact with skin, which provides greater user comfort.

#### Automatic harness: more comfortable, safer and faster adjustment.

Comfortable, flexible and adaptable for greatest comfort during prolonged periods of use. More comfortable double head and neck-strap system. This allows it to be worn on the neck when not in use. Front strap adjustment. Improved design with a greater inner volume, providing greater respiratory comfort. Greater respiratory comfort thanks to its two filters and exhalation valve. This model allows use in combination with other equipment. Filter attach with a threaded fitting, providing longer duration and lower respiratory resistance.

**Weight:** 165 g



Threaded filter



Automatic harness



Odourless rubber

Ref.	Product
911.745	Mask II Plus

#### Filters available:

Particles	P2 R, P3 R
Gases and vapours	A1, A2, B1, B2, E1, K1, K2
Multiple	AB1, ABE1, ABEK1, AB2EK1
Combined	A1P2R PAD, A2P2R PAD, B1P2R PAD, AB1P2R PAD, E1P2R PAD, K1P2R PAD, ABEK1P2R PAD, ABEK1P3R, ABEK1HgP3R

#### Complies with parameters established in EN 140

Number of filter holders	2	
Number of exhalation valves	1	
Number of inhalation valves	2	
CO2 content (%)	<1%	
Resistance to respiration (mbar)	<0,5	
To continual-flow inhalation	At 30 l/min	<1,3
	At 95 l/min	<2,0
	At 160 l/min	<3,0
To continual-flow exhalation at 160 l/min	<3,0	

## Respiratory protection: half masks

<b>Standard and certification</b>	EN 140
<b>Applications</b>	Environments with particle or gas contaminants. Do not use if the contaminant concentration exceeds 50 times the Permissible Exposure Limit.  Sectors: DIY, painting, mining, construction, woodworking, chemistry and laboratory,
<b>Conservation Storage - Expiry</b>	Store in its case in a cool, well ventilated place, avoiding humidity, dirt and dust.
<b>Directions Use</b>	It is advisable to clean after each use (except the filters) using soap and water. Air dry. Periodically, depending on degree of use, disinfect the product using a wide-spectrum antibacterial agent.
<b>Presentation</b>	1 unit per box. 32 boxes per carton Measurements: 150 x 150 x 102 mm
<b>Bar code</b>	GTIN-13: 8423173876586 GTIN-14: 18423173876583

