

Danubio



Prescription eye protection

Description and composition:

Metallic frame: resistant and very lightweight. Polycarbonate side protectors: highly resistant. Nose pads and temple tips in organic material.

Sizes: M: 52 x 16 mm / L: 54 x 18 mm / XL: 56 x 20 mm

Colour:

Weight: 32 g

Base: 5



Metallic frame



Nose pads in organic material



Polycarbonate side protectors

			MA	RKING
Ref:	Product Siz	ze	Lenses	Frame
906490	Polycarbonate spectacles. Anti-scratch cert. treatment	VI	M 1 FK CE	
900277	Polycarbonate spectacles. Anti-scratch cert. treatment	L	M 1 FK CE	
906492	Polycarbonate spectacles. Anti-scratch cert. treatment	(L	M 1 FK CE	
	with mineral safety prescription lenses		M 1 SK CE	M EN166 F CE
	with anti-scratch organic prescription lenses cert.		M 1 SK CE	
	with anti-scratch polycarbonate prescription lenses cert.		M 1 FK CE	

Prescription eye protection

Standard and certification	EN 166
Applications	Impact protection. Modern and light spectacles, highly recommendable for plant technicians, parts inspectors and office workers with occasional warehouse and production plant visits
Conservation Storage - Expiry	In order to maintain the spectacles in good condition, keep them in a clean, dry place in their appropriate case.
Directions	Cleaning: use tepid water and a neutral soap. Do not use abrasives or solvents. Rinse in water
Use	and dry with a soft cloth. Medop anti-fogging cleaning spray is also recommended. We advise regular inspection of the protectors, and their replacement if they have deteriorated in any way. Please ensure that the risk present in the workplace corresponds with the field of use of these protectors.
Presentation	and dry with a soft cloth. Medop anti-fogging cleaning spray is also recommended. We advise regular inspection of the protectors, and their replacement if they have deteriorated in any way. Please ensure that the risk present in the workplace corresponds with the field of
	and dry with a soft cloth. Medop anti-fogging cleaning spray is also recommended. We advise regular inspection of the protectors, and their replacement if they have deteriorated in any way. Please ensure that the risk present in the workplace corresponds with the field of use of these protectors. NEUTRAL sale units: 12 units per box. 25 boxes per carton.
Presentation	and dry with a soft cloth. Medop anti-fogging cleaning spray is also recommended. We advise regular inspection of the protectors, and their replacement if they have deteriorated in any way. Please ensure that the risk present in the workplace corresponds with the field of use of these protectors. NEUTRAL sale units: 12 units per box. 25 boxes per carton. (Prescription lens spectacles: no minimum units required)

Opcional treatments



Lenses 3 times more resistant to abrasion

Anti - reflective technology

Repels water and dust

Recommended for:

- >Surface dirt.
- >Suspended dust.
- >Presence of grease. >Small splash of water



Gendurance

Lenses 3 times more resistant to abrasion $N \Omega_{\rm acr}$

Anti - reflective technology

Repels water and dust

Repels water and dust

Recommended for:

- > Everyone that works using blue light.
- >Office workers
- > Workers under strip lighting or spotlights.
- >Workers using displays continually



Lenses 3 times more resistant to abrasion

Anti - reflective technology

Avoids lens fogging

Recommended for:

- > Temperature changes
- >Steam emissions
- >Use of respiratory protection
- >Physical labour

