



# LUKA



Clear



Polarised



Solar

## Neutral eye protection

### Description and composition:

Nylon sports frames for excellent protection and comfort.

**3 millimetre thick foam interior** allows a perfect fit to the face of the user and improves comfort. It is an accessory which can be removed.

A **very versatile model** with certified clear, solar, polarized and photochromic lenses.

Maximum **comfort** thanks to flat temples, perfect compatibility with other PPEs.

Highly impact-resistant polycarbonate lenses with **UV 400 filter**: 100% protection against harmful ultra-violet light.

**F marking**: Resistance to low-energy impact.

**Colour:** ●

**Weight:** 35 g



Flat and thin temples



Foam interior that provides comfort and fit



Wide range of CE lenses

Ref.	Product	Marking
912903	Clear polycarbonate anti-scratch and anti-fogging spectacles	2C-1.2 MEDOP 1 F
912886	Polycarbonate anti-scratch and anti-fogging sunglasses	5-2.5 Medop 1 F
912887	Polarized polycarbonate anti-scratch spectacles	5-3.1 Medop 1 F

## Neutral eye protection

<b>Standard and certification</b>	EN-166 EN-169 EN-170 EN-172									
<b>Applications</b>	Protection against low-energy impacts.  Industries: mining, quarries, aeronautics, renewable energy, refineries, automotive industry, sports, transport, maintenance, electronics. And in general any outdoor or indoor work with risk of impact.									
<b>Conservation Storage - Expiry</b>	In order to maintain the spectacles in good condition, keep them in a clean, dry place in their appropriate case.									
<b>Instructions Use</b>	Polycarbonate cleaning: use warm water and a neutral soap. Do not use abrasives or solvents. Rinse in water and dry with a soft cloth. Medop anti-fogging cleaning spray is also recommended. We advise regular inspection of the protectors, and their replacement if they have deteriorated in any way.									
<b>Presentation</b>	Individual polybag with bar code 12 units per box 10 boxes per carton									
<b>Bar code</b>	<table border="1"> <tr> <td data-bbox="552 1021 711 1048"><b>912903</b></td> <td data-bbox="751 1021 1007 1048">GTIN-13: 8.423.173.888.909</td> <td data-bbox="1066 1021 1331 1048">GTIN-14: 18.423.173.888.678</td> </tr> <tr> <td data-bbox="552 1055 711 1081"><b>912886</b></td> <td data-bbox="751 1055 1007 1081">GTIN-13: 8.423.173.888.664</td> <td data-bbox="1066 1055 1331 1081">GTIN-14: 18.423.173.888.661</td> </tr> <tr> <td data-bbox="552 1088 711 1115"><b>912887</b></td> <td data-bbox="751 1088 1007 1115">GTIN-13: 8.423.173.888.671</td> <td data-bbox="1066 1088 1331 1115">GTIN-14: 18.423.173.888.906</td> </tr> </table>	<b>912903</b>	GTIN-13: 8.423.173.888.909	GTIN-14: 18.423.173.888.678	<b>912886</b>	GTIN-13: 8.423.173.888.664	GTIN-14: 18.423.173.888.661	<b>912887</b>	GTIN-13: 8.423.173.888.671	GTIN-14: 18.423.173.888.906
<b>912903</b>	GTIN-13: 8.423.173.888.909	GTIN-14: 18.423.173.888.678								
<b>912886</b>	GTIN-13: 8.423.173.888.664	GTIN-14: 18.423.173.888.661								
<b>912887</b>	GTIN-13: 8.423.173.888.671	GTIN-14: 18.423.173.888.906								

